

RESIN MIXER

The model RM-1000 resin mixing machine is designed to mix messy resins with no cleanup.

The mixer base adjusts to grip your container and rotates it while a stationary mixing paddle creates turbulent mixing. The speed of mixing can be precisely controlled for bubble-free mixing with any resin. After mixing is done, just throw away the disposable cup and paddle, which means **NO CLEANUP!**


The adjustable chuck grabs your cup quickly by simply rotating the top disc until it tightens the grippers onto your mixing container. It accommodates mixing containers up to 106 mm [4.2 inches] across the base which should hold approximately 1000 ml. [34oz]

Once the cup is set in the chuck, insert a disposable paint paddle in the “stick holder”.

The stick-holder allows you to position the paddle in any position for optimum mixing. After that, turn on the motor to desired speed.

The no-cleanup design is a must for labs or small production operations when mixing frequently. Useful for epoxy resins, polyester resins, paints, adhesives - any messy liquid.

More info and product video at our website: www.gizmo-engineering.com



MODEL RM-1000

